



## Product description

Order number	90.170.350
Product description	Gas sampler, GS 301, incl. mains adapter GN 100?240/15 V, feed rate: 0.1 - 1.5 l/min, feed volume: 0.1 - 9,999.9 l

## Product characteristics

Power consumption during operation	15 W
------------------------------------	------

## Size

Width of product	255 mm
Length of product	290 mm

## Purity & certification

Product category	Appliance, according to machinery or equipment directive, CE
CE certified	CE
Batched	no

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.

This specification is confidential and the property of Sarstedt. It is neither to be duplicated nor made available to third parties without our prior written consent.





### **Packaging**

Minimum order qty.	1
Type of inner packaging	case
Piece(s) / inner box	1
Piece(s) / case	1
Case volume	0.0363 cbm
Weight of product	5.5 kg
Weight of case	6.5 kg
EAN of inner box	4038917101189
EAN case	4038917051507

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.

This specification is confidential and the property of Sarstedt. It is neither to be duplicated nor made available to third parties without our prior written consent.

