



Product description

Order number	67.742
Product description	Semi-micro cuvette, max. working volume: 3 ml, material: PS, transparent, (HxW): 45 x 12 mm, optical sides: 2, path length: 10 mm, sorted by mould cavity number, 100 piece(s)/polystyrene container

Product characteristics

Volume of work	1 ml - 3 ml
Number of optical sides	2
Path length	10 mm
Wavelength in the cuvette area	330 nm

Size

Max. volume	3 ml
Width of product	12 mm
Height of product	45 mm

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.





Product Specification
Semi-micro cuvette, 3 ml, (HxW): 45 x 12 mm, PS,
transparent, optical sides: 2

Page 2

Material & colours

Product material Polystyrene (PS)
Colour of product transparent

Purity & certification

Product category not regulated
CE certified no CE mark
Batched no

Packaging

Minimum order qty. 2000
Type of smallest
subpackaging polystyrene container
Piece(s) / inner box 100
Piece (s) / outer case 2000
Piece(s) / pallet 48000
Depth of case 458 mm
Width of case 288 mm
Height of case 415 mm
Case volume 0.0547 cbm
Weight of product 0.0023 kg
Weight of case 5.85 kg
EAN of inner box 4038917083881
EAN case 4038917002769

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.

Date of issue:
2026-03-17

This document was prepared by EDP support and is valid without signature.



SARSTEDT