



### Product description

Order number	60.9921.530
Product description	Screw cap tube, working volume: 5 ml, (LxØ): 50 x 16 mm, material: PS, flat base, transparent, screw cap, natural, cap enclosed, 250 piece(s)/bag

### Product characteristics

Graduation	no
Cap	standard screw cap
Closure type	screw cap
Base shape	flat base
Volume of work	5 ml
Centrifugation max (RCF)	5000 x g
Centrifugation temperature	21
Centrifugation time	15 Min

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.





### **Size**

Diameter	16 mm
Length of product	50 mm

### **Material & colours**

Product material	Polystyrene (PS)
Colour of product	transparent
Closure material	High Density Polyethylene (HD-PE)
Colour of cap	natural
Tube material	Polystyrene (PS)

### **Purity & certification**

Satisfies the requirement	sealed at 18"hg/10min
Latex-free	yes
Pyrogen-free	no
Safety data sheet	no

### **Packaging**

Minimum order qty.	2000
Type of smallest subpackaging	bag
Piece(s) / inner box	250
Piece (s) / outer case	2000
Piece(s) / pallet	80000
Depth of case	604 mm
Width of case	264 mm
Height of case	373 mm
Case volume	0.0595 cbm
Weight of case	9 kg
EAN of inner box	4038917150859
EAN case	4038917037174

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.

