



**Product description**

Order number	67.759
Product description	UV cuvette, max. working volume: 2 ml, material: special plastic, transparent, (HxW): 45 x 12.5 mm, optical sides: 2, suitable for use beginning at 220 nm, path length: 10 mm, centre height: 15 mm, sorted by mould cavity number, 100 piece(s)/polystyrene container

**Product characteristics**

Application	suitable for use beginning at 220 nm
Volume of work	50 µl - 2 ml
Number of optical sides	2
Path length	10 mm
Centre height	15 mm
Wavelength in the cuvette area	220 nm

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.





**Size**

Max. volume	2.5 ml
Width of product	12.5 mm
Height of product	45 mm

**Material & colours**

Product material	special plastic
Colour of product	transparent

**Purity & certification**

Product category	no medical device   IVD
Batched	yes

**Packaging**

Minimum order qty.	400
Type of smallest subpackaging	polystyrene container
Piece(s) / inner box	100
Piece (s) / outer case	400
Piece(s) / pallet	31200
Depth of box	222 mm
Width of box	202 mm
Height of box	56 mm
Depth of case	418 mm
Width of case	278 mm
Height of case	130 mm
Case volume	0.0151 cbm
Weight of product	0.0015 kg
Weight of case	1.29 kg
EAN of inner box	4038917264471
EAN case	4038917264464

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.

